




Note:



L(Length)	T(Tolerance)	Part number	Color
1000	20	SN35-3/18/1BK	BLK
1000	20	SN35-3/18/1WH	WHT
1000	20	SN35-3/18/1GY	GRY
1800	50	SN35-3/18/1.8BK	BLK
1800	50	SN35-3/18/1.8WH	WHT
1800	50	SN35-3/18/1.8GY	GRY
3000	50	SN35-3/18/3BK	BLK
3000	50	SN35-3/18/3WH	WHT
3000	50	SN35-3/18/3GY	GRY
5000	50	SN35-3/18/5BK	BLK
5000	50	SN35-3/18/5WH	WHT
5000	50	SN35-3/18/5GY	GRY



NOTE :

1. PLUG : LT-202 AMERICAN TYPE
2. CONNECTOR : LT-535 IEC 60320 C5
3. Strain relief : NA
4. CORD : SVT 3X18AWG 105D
5. APPROVALS : UL, C-UL
6. CUSTOMER : TME
7. Supplier for flexible cord : RHYTHM, I-SHENG, STANDARD, WU LI
8. P/N : Above Note Chart

修改履歷

6		
5		
4		
3		
2		
1	新增	22/09/28
REV.	DESCRIPTION	DATE

DRAWER	Aaron	DATE	22/09/28	TITLE	LT-202+535
APPROVE		REV.	1	Dr.No.	1110962
		TOL.	±5mm		
		ALL DIMENSIONS IN mm			

※Customer drawing number : NA



LIAN DUNG
ELECTRIC WIRE MATERIAL CO.,LTD.
聯東電線材料股份有限公司