




FOR 客户名称	APPROVED 客户确认签字	ATTN 销售负责人


THE SHADED PART IS ILLUMINATED

PANEL CUTOUT

SEAL RING

PART NUMBER: ONPOW6119F-11■E/△/▲/S

Schematic



"■"	OPERATION MODE	"△"	LAMP COLOR	"▲"	LAMP VOLTAGE
NO LETTER	MOMENTARY	R	RED	6V	AC/DC 6V
Z	LATCHING	G	GREEN	12V	AC/DC 12V
		Y	YELLOW	24V	AC/DC 24V
		B	BLUE	110V	AC/DC 110V
		W	WHITE	220V	AC/DC 220V
OTHER VOLTAGE CAN BE MADE TO ORDER					

SPECIFICATIONS:

- 1.SWITCH RATING: AC220V/0.5A.
- 2.MECHANICAL LIFE: ≥1,000,000 cycles.
- 3.ELECTRICAL LIFE: ≥50,000 cycles.
- 4.CONTACT RESISTANCE: ≤50mΩ.
- 5.INSULATION RESISTANCE: ≥100MΩ(500VDC).
- 6.DIELECTRIC STRENGTH: 1,500V, RMS 50HZ, 1min.
- 7.OPERATING TEMPERATURE: -25℃~ +55℃(NO FREEZING).
- 8.OPERATING FORCE: ABOUT 2.5N.
- 9.OPERATING TRAVEL: ABOUT 3mm.
- 10.TORQUE: ABOUT 0.6Nm MAX.APPLIED TO NUT.
- 11.IP CLASS: IP40(IP65 CAN MADE TO ORDER), IK07.
- 12.TERMINAL TYPE: PIN TERMINAL(2.8 X 0.5mm).
- 13.GENERAL TOLERANCE:0-18mm=±0.25, 18-80mm=±0.52.

MATERIALS:

- 1.CONTACT: SILVER ALLOY.
- 2.BUTTON: STAINLESS STEEL.
- 3.BODY: STAINLESS STEEL.
- 4.BASE: PA.

BRAND 品牌	红波按钮制造有限公司				
ONPOW 欧宝龙®	ONPOW PUSH BUTTON MANUFACTURE CO.,LTD.				
TITLE 名称	ONPOW61 SERIES ANTI-VANDAL PUSH BUTTON		UNIT 单位	mm	
FILE NAME 档案名称	ONPOW6119F-E	SCALE 比例	1.2 : 1	SIZE 图纸	A4
DWG NO. 图号	ONPOW6119-E .DWG	DRAWN 制图	YDY 2022/06/30	SHEET 张	1/1
				REV. 更改	1