

Product data sheet

502 030 6

Pipe Cutter for composite and protective pipes

Without calibration arbour

- Precise right-angle cutting of aluminum composite and plastic pipes from 12 to 25 mm diameter
- Clean, smooth, burr-free cuts
- Safe cutting of corrugated outer protective pipe without damaging the inner pipe
- Short cutting distances (90°) allow cutting of protective outer pipe when installed
- Option to install calibration arbour, e.g. for Geberit pipes of 11.5 and 15 mm diameter
- Replaceable blades
- Also available without outer pipe cutting attachment
- Ergonomically designed two-component handles



General

Item number	502 030 6
EAN	4049002015908
Weight	378 g
Dimension	210 mm
Dimension packaging	75 x 25 x 240 mm

Specifications

Composite pipe	12 – 25 mm
Protective pipe	18 – 35 mm

Classification

eCl@ss 10.1	ACC523013
ETIM 7.0	EC000160
proficl@ss 7.0	AAA520c003

Spare Parts

502 021 0 0	Replacement rectangular blade
502 022 0 0	Replacement blade for protective pipe

With reservations regarding technical modifications and errors. Illustration may vary.