



Product: [8504](#)

Lead Wire, #24 Str TC, PVC Ins, TYPE B MIL-W-16878/1

Request Sample

Product Description

Low Temp Plastic Lead Wire, 24AWG (7x32) Tinned Copper, PVC Insulation, TYPE B MIL-W-16878/1 600V 105C

Technical Specifications

Product Overview

Suitable Applications:	inter-connection circuits, internal wiring of computer and electronic equipments, (Type B) MIL-W-16878/1-Low Temp applications
------------------------	--

Construction Details

Conductor

Element	Number of Element	Size	Stranding	Material
Conductor(s)	1	24	7x32	TC - Tinned Copper

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter
PVC - Polyvinyl Chloride	0.01 in (0.25 mm)	0.044 in (1.1 mm)

Overall Cable Diameter (Nominal):	0.044 in (1.1 mm)
-----------------------------------	-------------------

Electrical Characteristics

Voltage

UL Voltage Rating
600 V RMS

Mechanical Characteristics

Bend Radius

Stationary Min.	Installation Min.
0.18 in (4.6 mm)	0.18 in (4.6 mm)

Max. Pull Tension:	5.5 lbs (2.5 kg)
Bulk Cable Weight:	2 lbs/1000ft

Standards and Compliance

Sustainability:	CA Prop 65
Military Compliance:	MIL-W-16878/1
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)

History

Update and Revision:	Revision Number: 0.409 Revision Date: 11-09-2022
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
8504 010100	Black	Reel	100 ft	612825210313

8504 0101000	Black	Reel	1,000 ft	612825210320
8504 006100	Blue, Light	Reel	100 ft	612825210207
8504 0061000	Blue, Light	Reel	1,000 ft	612825210214
8504 001100	Brown	Reel	100 ft	612825210054
8504 0011000	Brown	Reel	1,000 ft	612825210061
8504 008100	Gray	Reel	100 ft	612825210238
8504 0081000	Gray	Reel	1,000 ft	612825210245
8504 005100	Green, Dark	Reel	100 ft	612825210177
8504 0051000	Green, Dark	Reel	1,000 ft	612825210184
8504 003100	Orange	Reel	100 ft	612825210115
8504 0031000	Orange	Reel	1,000 ft	612825210122
8504 002100	Red	Reel	100 ft	612825210085
8504 0021000	Red	Reel	1,000 ft	612825210092
8504 0071000	Violet	Reel	1,000 ft	612825210221
8504 009100	White	Reel	100 ft	612825210269
8504 0091000	White	Reel	1,000 ft	612825210276
8504 004100	Yellow	Reel	100 ft	612825210146
8504 0041000	Yellow	Reel	1,000 ft	612825210153

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.