

PRODUCT-DETAILS

696-41795

CBL TIE LKG HEAD BLK ACETAL BULK PK



General Information

Extended Product Type	696-41795
Product ID	7TAA159090R0001
EAN	5414363126744
Catalog Description	CBL TIE LKG HEAD BLK ACETAL BULK PK
Long Description	Deltec Cable Tie Locking Head Only, Black Acetal for Temperatures up to 85 Degrees Celsius (185 F), Length of 21.59mm (0.85 Inches), Width of 19.05mm (0.75 Inch), Height of 12.57mm (0.495 Inch), Weather and Ultraviolet Resistant, Bulk Pack

Ordering

EAN	5414363126744
UPC	786210066752
Country of Origin	United States (US)
Customs Tariff Number	3926909985
Selling Unit of Measure	each

Dimensions

Product Net Width	0.75 in 19.05 mm
Product Net Depth / Length	0.85 in 21.59 mm

Container Information

Package Level 1 Units	500 piece
Package Level 2 Units	1000 piece
Package Level 2 Width	8 in 203 mm
Package Level 2 Height	6.5 in 165 mm
Package Level 2 Depth / Length	11.3 in 287 mm

Technical UL/CSA

Flammability According to UL94	HB
--------------------------------	----

Additional Information

Application	Ideal solution for bundling in harsh outdoor environments.
Brand / Label	Deltec
Color	Black
Effective Date	19880325
Lock Type	Double Locking Head
Material	Weather Resistant Acetel
Product Name	SELF LOCK PLASTIC HEAD FOR CABLETIE
Product Type	Head (Buckle)
RoHS Date	9AKK108466A7853
Special Functions	Perfect for coaxial, fiber optic and all other communication and electrical conducting cables.
Tensile Strength	250 lb 1112 N

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	696-41795
Instructions and Manuals	696-41795
REACH Declaration	9AKK108466A7852
RoHS Information	9AKK108466A7853

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

