

PRODUCT-DETAILS

SRPE-8-0

SPIRAL WRAP UV BLK POLYETHYL 8MMOD



General Information

Extended Product Type	SRPE-8-0
Product ID	7TCG054090R0238
EAN	5414363174677
Catalog Description	SPIRAL WRAP UV BLK POLYETHYL 8MMOD
Long Description	Spiral Wrap, Black Polyethylene for Temperatures up to 100 Degrees Celsius (212 F), Weather and Ultraviolet Resistant, Outer Diameter of 8mm (0.315 Inch), Pitch of 10.8mm (0.425 Inch), Nominal Thickness of 0.5mm (0.196 Inch), Minimum Bundle Diameter of 6mm (0.236 Inch), Maximum Bundle Diameter of 60mm (2.36 Inches), Length of 10m (32.81 Feet)

Ordering

EAN	5414363174677
UPC	728494141718
Country of Origin	Thailand (TH)
Customs Tariff Number	3926909990
Selling Unit of Measure	roll

Container Information

Package Level 1 Units	1 reel
Package Level 1 Width	8.64 in 219 mm
Package Level 1 Height	0.24 in 6 mm
Package Level 1 Depth / Length	8.64 in 219 mm
Package Level 2 Units	60 reel

Package Level 2 Width	16.73 in 425 mm
Package Level 2 Height	13.58 in 345 mm
Package Level 2 Depth / Length	16.73 in 425 mm

Additional Information

Application	For Temperatures up to 100 Degrees Celsius (212 F)
Brand / Label	Catamount
Color	Black
Effective Date	20051206
Material	Polyethylene
Outside Diameter	0.31 in 8 mm
Pitch	0.43 in ; 10.8 mm
Product Name	PLASTIC CONDUIT
Product Type	Spiral Wrap
Temperature Range	-40 to 212 °F -40 to 100 °C
Wall Thickness	0.02 in 0.5 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	SRPE-8-0
Instructions and Manuals	SRPE-8-0

Classifications

ETIM 6	EC002604 - Cable bundle hose
ETIM 7	EC002604 - Cable bundle hose
ETIM 8	EC002604 - Cable bundle hose
UNSPSC	39131604
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5395 >> Spiral wrapping

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

