



PRODUCT-DETAILS

TB-12-50RLDH

CABLE TIE 50LB 12IN NAT NYL DBL HEA



General Information

Extended Product Type	TB-12-50RLDH
Product ID	7TCG054360R0057
EAN	5414363055921
Catalog Description	CABLE TIE 50LB 12IN NAT NYL DBL HEA
Long Description	Double Loop Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length 300mm(11.81 Inches), Width 4.82mm (0.19 Inches), Tensile Strength Rating of 220 Newtons (50 Pounds)

Ordering

EAN	5414363055921
UPC	786210863993
Country of Origin	Thailand (TH)
Customs Tariff Number	3926909990
Selling Unit of Measure	each

Dimensions

Product Net Width	0.19 in 4.82 mm
Product Net Depth / Length	11.8 in 300 mm

Container Information

Package Level 1 Units	1000 piece
Package Level 2 Units	11000 piece
Package Level 2 Width	15.7 in 399 mm
Package Level 2 Height	15.7 in 399 mm
Package Level 2 Depth / Length	19.6 in 498 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Catamount
Color	Natural
Effective Date	20021118
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6
Product Name	OTHER PLASTICS ITEMS
Product Type	Double Loop
Special Functions	Enables parallel routing of two cable bundles with one single cable tie.
Tensile Strength	50 lb 220 N

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TB-12-50RLDH
Instructions and Manuals	TB-12-50RLDH

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

