



PRODUCT-DETAILS

TS2845HF

CABLE TIE 50LB NAT NYL 11IN FLM RET



General Information

Extended Product Type	TS2845HF
Product ID	7TCG054360R0065
EAN	5414363059943
Catalog Description	CABLE TIE 50LB NAT NYL 11IN FLM RET
Long Description	Flame Retardant Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Length 280mm (11.02 Inches), Width 4.5mm (0.177 Inches), Tensile Strength Rating of 220 Newtons (50 Pounds)

Ordering

EAN	5414363059943
UPC	786210623184
Country of Origin	Thailand (TH)
Customs Tariff Number	3926909985
Selling Unit of Measure	each

Container Information

Package Level 1 Units	100 piece
Package Level 2 Units	11000 piece

Technical UL/CSA

Flammability According to UL94	V-0
--------------------------------	-----

Additional Information

Brand / Label	Catamount
Bundle Diameter	3 in 76.2 mm
Color	Natural
Effective Date	19980621
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6
Product Name	CATAMOUNT FASTENING PRODUCTS
Product Type	Flame Retardant
Tensile Strength	50 lb 222 N

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TS2845HF
Instructions and Manuals	TS2845HF
REACH Declaration	9AKK108466A3876
RoHS Information	9AKK108466A3872

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

