



PRODUCT-DETAILS

TY125-40-2-100

TY-FAST 3,6 X 141MM RED



General Information

Extended Product Type	TY125-40-2-100
Product ID	7TCG054360R0128
EAN	5414363060574
Catalog Description	TY-FAST 3,6 X 141MM RED
Long Description	Cable Tie, Red Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 140mm (5.51 Inches), Width of 3.6mm (0.14 Inches), Thickness of 1.2mm (0.05 Inches), Tensile Strength Rating of 178 Newtons (40 Pounds), 100 Pack

Ordering

EAN	5414363060574
UPC	786210840963
Replacement Product ID (NEW)	7TAG009160R0017
Country of Origin	Hungary (HU)
Customs Tariff Number	3926909990
Selling Unit of Measure	each

Container Information

Package Level 1 Units	100 piece
Package Level 1 Width	5 in 127 mm

Package Level 1 Height	2 in 51 mm
Package Level 1 Depth / Length	9 in 229 mm
Package Level 2 Units	10000 piece
Package Level 2 Width	10.2 in 259 mm
Package Level 2 Height	13.8 in 351 mm
Package Level 2 Depth / Length	19.7 in 500 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Catamount
Bundle Diameter	1.25 in 31.75 mm
Color	Red
Effective Date	20020514
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6
Product Name	OTHER ARTICLES OF PLASTICS
Product Type	General Purpose
Tensile Strength	40 lb 180 N
Thickness	0.05 in 1.2 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY125-40-2-100
Instructions and Manuals	TY125-40-2-100

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

