



PRODUCT-DETAILS

TY200-120X-100

CABLE TIE 120LB 9IN UV BLACK NYLON



General Information

Extended Product Type	TY200-120X-100
Product ID	7TCG054360R0189
EAN	5414363126768
Catalog Description	CABLE TIE 120LB 9IN UV BLACK NYLON
Long Description	Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, Length of 200mm (7.87 Inches), Width of 7.6mm (0.30 Inches), Thickness of 1.6mm (0.06 Inches), Tensile Strength Rating of 534 Newtons (120 Pounds), 100 Pack

Ordering

EAN	5414363126768
Replacement Product ID (NEW)	7TCG054360R0438
Country of Origin	Hungary (HU)
Customs Tariff Number	3926909990
Selling Unit of Measure	each

Dimensions

Product Net Width	0.3 in 7.62 mm
Product Net Depth / Length	7.87 in 200 mm

Container Information

Package Level 1 Units	100 piece
Package Level 2 Units	2500 piece
Package Level 2 Width	10.2 in 259 mm
Package Level 2 Height	9.1 in 231 mm
Package Level 2 Depth / Length	19.7 in 500 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Catamount
Bundle Diameter	2 in 50.8 mm
Color	Black
Effective Date	19980708
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6
Product Name	CATAMOUNT FASTENING PRODUCTS
Product Type	General Purpose
Standards	UL E49405
Tensile Strength	120 lb 540 N
Thickness	0.06 in 1.6 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY200-120X-100
Declaration of Conformity - CE	9AKK107492A9843
Instructions and Manuals	TY200-120X-100
REACH Declaration	9AKK108466A3876
RoHS Information	9AKK108466A3872

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

