

PRODUCT-DETAILS

TY271MX

CABLE TIE 120LB 6IN UV BLACK NYLON



General Information

Extended Product Type	TY271MX
Product ID	7TCG009450R0163
EAN	5414363062950
Catalog Description	CABLE TIE 120LB 6IN UV BLACK NYLON
Long Description	High Performance Cable Tie, Black Color Nylon 6.6, Length of 150mm (5.9 Inches) for Bundle Diameter up to 25mm (0.98 Inch), Width of 6.9mm (0.27 Inch), Tensile Strength Rating of 534 Newtons (120 Pounds), Operating Temperature of -40 Degrees Celsius (-40 F) to 105 Degrees Celsius (221 F), Bulk Pack

Ordering

EAN	5414363062950
UPC	786210470436
Country of Origin	Hungary (HU)
Customs Tariff Number	3926909990
Selling Unit of Measure	each

Container Information

Package Level 1 Units	500 piece
Package Level 2 Units	5000 piece
Package Level 2 Width	10.2 in 259 mm
Package Level 2 Height	13.8 in 351 mm
Package Level 2 Depth / Length	19.7 in 500 mm

Technical UL/CSA	
Flammability According to UL94	V-2

Additional Information	
Brand / Label	Ty-Rap
Bundle Diameter	Max 0.98 in Max 25 mm
Color	Black
Effective Date	19980621
Lock Type	Stainless Steel Barb
Product Name	PLASTIC CABLE TIE
Product Type	High Performance
Standards	UL E49405
Tensile Strength	120 lb 534 N
Thickness	0.06 in 1.5 mm

Certificates and Declarations (Document Number)	
Data Sheet, Technical Information	TDS000487
Instructions and Manuals	TY271MX

Classifications	
ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories	
Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties	

