



PRODUCT-DETAILS

TY271M

CABLE TIE 120LB 6IN NATURAL NYLON



General Information

Extended Product Type	TY271M
Product ID	7TCG009450R0162
EAN	5414363062943
Catalog Description	CABLE TIE 120LB 6IN NATURAL NYLON
Long Description	High Performance Cable Tie, Natural Color Nylon 6.6, Length of 150mm (5.9 Inches) for Bundle Diameter up to 25mm (0.98 Inch), Width of 6.9mm (0.27 Inch), Tensile Strength Rating of 540 Newtons (120 Pounds), Operating Temperature of -20 Degrees Celsius (-4F) to 85 Degrees Celsius (185 F), Bulk Pack

Ordering

EAN	5414363062943
UPC	786210543451
Country of Origin	Hungary (HU)
Customs Tariff Number	3926909990
Selling Unit of Measure	each

Container Information

Package Level 1 Units	500 piece
Package Level 2 Units	5000 piece
Package Level 2 Width	10.2 in 259 mm
Package Level 2 Height	13.8 in

	351 mm
Package Level 2 Depth /	19.7 in
Length	500 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Ty-Rap
Bundle Diameter	Max 0.98 in Max 25 mm
Color	Natural
Effective Date	19980621
Lock Type	Stainless Steel Barb
Product Name	PLASTIC CABLE TIE
Product Type	High Performance
Standards	UL E49405
Tensile Strength	120 lb 540 N
Thickness	0.06 in 1.5 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TDS000487
Instructions and Manuals	TY271M

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

