



PRODUCT-DETAILS

TY300-50-4

CABLE TIE 50LB 12IN YEL NYLON



General Information

Extended Product Type	TY300-50-4
Product ID	7TCG054360R0269
EAN	5414363064107
Catalog Description	CABLE TIE 50LB 12IN YEL NYLON
Long Description	Cable Tie, Yellow Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 300mm (11.81 Inches), Width of 4.8mm (0.19 Inches), Thickness of 1.3mm (0.05 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds), Bulk Pack

Ordering

EAN	5414363064107
UPC	786210766591
Replacement Product ID (NEW)	7TAG009270R0009
Country of Origin	Hungary (HU)
Customs Tariff Number	3926909990
Selling Unit of Measure	each

Dimensions

Product Net Width	0.19 in 4.8 mm
Product Net Depth / Length	8.46 in 215 mm

Container Information

Package Level 1 Units	1000 piece
Package Level 1 Width	15 in 381 mm
Package Level 1 Height	4 in 102 mm
Package Level 1 Depth / Length	21 in 533 mm
Package Level 2 Units	5000 piece
Package Level 2 Width	14 in 356 mm
Package Level 2 Height	13 in 330 mm
Package Level 2 Depth / Length	19 in 483 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Catamount
Bundle Diameter	3 in 76.2 mm
Color	Yellow
Effective Date	19970904
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6
Product Name	CATAMOUNT FASTENING PRODUCTS
Product Type	General Purpose
Tensile Strength	50 lb 222 N
Thickness	0.05 in 1.3 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY300-50-4
Declaration of Conformity - CE	9AKK107492A9843
Instructions and Manuals	TY300-50-4

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

