



PRODUCT-DETAILS

TY5244MR

CABLE TIE 30LB 14.5IN NATURAL NYLON



General Information

Extended Product Type	TY5244MR
Product ID	7TCG009110R0023
EAN	5414363065470
Catalog Description	CABLE TIE 30LB 14.5IN NATURAL NYLON
Long Description	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 368.3mm (14.5 Inches), Width of 3.61mm (0.142 Inches), Thickness of 1.31mm (0.052 Inches), Tensile Strength Rating of 180 Newtons (40 Pounds), Euroslot Packaging

Ordering

E-Number (Finland)	1370033
EAN	5414363065470
UPC	786210633527
Country of Origin	Hungary (HU)
Customs Tariff Number	3926909990
Selling Unit of Measure	each

Dimensions

Product Net Width	0.142 in 3.6 mm
Product Net Depth / Length	14.5 in 368.3 mm

Container Information

Package Level 1 Units	100 piece
Package Level 2 Units	5000 piece
Package Level 2 Width	10.2 in 259 mm
Package Level 2 Height	13.8 in 351 mm
Package Level 2 Depth / Length	19.7 in 500 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Ty-Rap
Color	Natural
Effective Date	19980621
Lock Type	Stainless Steel Barb
Material	Nylon/Polyamide 6.6
Product Name	TY-RAP FASTENING
Product Type	High Performance
RoHS Date	9AKK107991A8366
Tensile Strength	40 lb 180 N
Thickness	0.05 in 1.31 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY5244MR
Declaration of Conformity - CE	9AKK107492A9841
Instructions and Manuals	TY5244MR
REACH Declaration	9AKK107992A8781
RoHS Information	9AKK107991A8366

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

