

PRODUCT-DETAILS

TY5271MXR

CABLE TIE 120LB 6IN UV BLACK NYLON



General Information

Extended Product Type	TY5271MXR
Product ID	7TCG009450R0181
EAN	5414363065746
Catalog Description	CABLE TIE 120LB 6IN UV BLACK NYLON
Long Description	Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (221 F), Weather and Ultraviolet Resistant Polyamide (Nylon 6.6) for Indoor or Outdoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 150mm (5.9 inches), Width of 6.9mm (0.27 Inch), Thickness of 1.5mm (0.06 inches), Tensile Strength Rating of 540 Newtons (120 Pounds), Euroslot Packaging

Ordering

EAN	5414363065746
UPC	786210634067
Country of Origin	Hungary (HU)
Customs Tariff Number	3926909990
Selling Unit of Measure	each

Dimensions

Product Net Width	0.3 in 7.6 mm
Product Net Depth / Length	5.9 in 150 mm

Container Information

Package Level 1 Units	50 piece
Package Level 2 Units	5000 piece
Package Level 2 Width	15.4 in 391 mm
Package Level 2 Height	11 in 279 mm
Package Level 2 Depth / Length	23.6 in 599 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Ty-Rap
Color	Black
Effective Date	19980621
Lock Type	Stainless Steel Barb
Material	Nylon/Polyamide 6.6
Product Name	TY-RAP FASTENING
Product Type	High Performance
Tensile Strength	120 lb 540 N
Thickness	0.06 in 1.5 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TDS000487
Instructions and Manuals	TY5271MXR

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

