

PRODUCT-DETAILS

TY527MFRR-RW

TY27MFR FOR RAILWAY SP



General Information

Extended Product Type	TY527MFRR-RW
Product ID	7TCG009570R0018
EAN	5415022243697
Catalog Description	TY27MFR FOR RAILWAY SP
Long Description	Cable Tie for Railway, Flame Retardant White Polyamide 6.6, Length of 343mm (13.5 Inches), Width of 7.6mm (0.30 Inch), Thickness of 1.5mm (0.06 Inch), Maximum Bundle Diameter 95mm (4.8 Inches), Tensile Strength Rating of 540 Newtons (121 Pounds), Small Pack

Ordering

EAN	5415022243697
UPC	786209884459
Country of Origin	Hungary (HU)
Customs Tariff Number	3926909990
Selling Unit of Measure	each

Container Information

Package Level 1 Units	50 piece
Package Level 1 Width	5.1 in 130 mm
Package Level 1 Height	1.17 in 30 mm
Package Level 1 Depth / Length	18.07 in 459 mm
Package Level 2 Units	2000 piece

Package Level 2 Width	10.21 in 259 mm
Package Level 2 Height	9.03 in 229 mm
Package Level 2 Depth / Length	19.65 in 499 mm

Technical UL/CSA

Flammability According to UL94	V-0
-----------------------------------	-----

Additional Information

Brand / Label	Ty-Rap
Bundle Diameter	0.19 to 3.74 in 4.8 to 95 mm
Color	White
Effective Date	20140612
Lock Type	Stainless Steel Barb
Product Name	OTHER PLASTICS ITEMS
Product Type	Railway
Tensile Strength	121 lb 540 N
Thickness	0.06 in 1.5 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TDS000478
Instructions and Manuals	TY527MFRR-RW

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

