

PRODUCT-DETAILS

TY54513M-2

CABLE TIE 175LB 45IN RED NYLON



General Information

Extended Product Type	TY54513M-2
Product ID	7TCG009380R0004
EAN	5415022150070
Catalog Description	CABLE TIE 175LB 45IN RED NYLON
Long Description	Cable Tie, Red Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 1143mm (45.0 Inches), Width of 8.13mm (0.32 Inch), Thickness of 1.7mm (0.07 Inch), Tensile Strength Rating of 780 Newtons (175 Pounds)

Ordering

EAN	5415022150070
UPC	786209599841
Country of Origin	Hungary (HU)
Customs Tariff Number	3926909990
Selling Unit of Measure	each

Dimensions

Product Net Width	0.32 in 8.13 mm
Product Net Depth / Length	45 in 1143 mm

Container Information

Package Level 1 Units	50 piece
Package Level 1 Width	7.08 in 180 mm
Package Level 1 Height	1.18 in 30 mm
Package Level 1 Depth / Length	49.6 in 1260 mm
Package Level 2 Units	250 piece
Package Level 2 Width	5.11 in 130 mm
Package Level 2 Height	5.51 in 140 mm
Package Level 2 Depth / Length	47.6 in 1209 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Ty-Rap
Color	Red
Effective Date	20130205
Lock Type	Stainless Steel Barb
Material	Nylon/Polyamide 6.6
Product Name	OTHER ARTICLES OF PLASTIC
Product Type	High Performance
Tensile Strength	175 lb 780 N
Thickness	0.07 in 1.7 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY54513M-2
Instructions and Manuals	TY54513M-2

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

