



PRODUCT-DETAILS

TY53510M-3

CABLE TIE 175LB 35IN ORANGE NYLON



General Information

Extended Product Type	TY53510M-3
Product ID	7TCG009400R0008
EAN	5414363174370
Catalog Description	CABLE TIE 175LB 35IN ORANGE NYLON
Long Description	Cable Tie, Orange Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 889mm (35.0 Inches), Width of 8.13mm (0.32 Inches), Thickness of 1.7mm (0.07 Inches), Tensile Strength Rating of 780 Newtons (175 pounds)

Ordering

EAN	5414363174370
UPC	786210982236
Country of Origin	Hungary (HU)
Customs Tariff Number	3926909990
Selling Unit of Measure	each

Dimensions

Product Net Width	0.32 in 8.13 mm
Product Net Depth / Length	35 in 889 mm

Container Information

Package Level 1 Units	50 piece
Package Level 1 Width	5 in 127 mm
Package Level 1 Height	1 in 25 mm
Package Level 1 Depth / Length	35 in 889 mm
Package Level 2 Units	250 piece
Package Level 2 Width	5.1 in 130 mm
Package Level 2 Height	5.1 in 130 mm
Package Level 2 Depth / Length	38.2 in 970 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Ty-Rap
Color	Orange
Effective Date	20051108
Lock Type	Stainless Steel Barb
Material	Nylon/Polyamide 6.6
Product Name	NYLON DUCT TIE
Product Type	High Performance
Tensile Strength	175 lb 780 N
Thickness	0.07 in 1.7 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY53510M-3
Instructions and Manuals	TY53510M-3

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

