



PRODUCT-DETAILS

TYH272M

CABLE TIE 120LB 9IN GR NYL HEAT STB



General Information

Extended Product Type	TYH272M
Product ID	7TCG009590R0008
EAN	5414363067443
Catalog Description	CABLE TIE 120LB 9IN GR NYL HEAT STB
Long Description	Cable Tie, Heat Stabilized Polyamide (Nylon 6.6) - Greenish Tint, for Temperatures up to 105 Degrees Celsius (220 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 343mm (13.5 Inches), Width of 6.9mm (0.27 Inch), Thickness of 1.5mm (0.06 Inch), Tensile Strength Rating of 540 Newtons (120 Pounds)

Ordering

EAN	5414363067443
UPC	786210520087
Country of Origin	Hungary (HU)
Customs Tariff Number	3926909990
Selling Unit of Measure	each

Dimensions

Product Net Width	0.275 in 6.99 mm
Product Net Depth / Length	8.75 in 225.25 mm

Container Information

Package Level 1 Units	500 piece
Package Level 2 Units	5000 piece
Package Level 2 Width	10.2 in 259 mm
Package Level 2 Height	13.8 in 351 mm
Package Level 2 Depth / Length	19.7 in 500 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Ty-Rap
Bundle Diameter	0.19 to 2.01 in 4.8 to 51 mm
Color	Green Tint
Effective Date	19980621
Lock Type	Stainless Steel Barb
Material	Nylon/Polyamide 6.6
Product Name	TY-RAP FASTENING
Product Type	Heat-Stabilized
RoHS Date	9AKK108466A3874
Standards	UL E49405
Tensile Strength	120 lb 534 N
Thickness	0.06 in 1.5 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TDS000494
Instructions and Manuals	TYH272M
REACH Declaration	9AKK108466A3877
RoHS Information	9AKK108466A3874

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

