



PRODUCT-DETAILS

TYG534MX

CABLE TIE 40LB 6IN BLK NYL BLIND MT



General Information

Extended Product Type	TYG534MX
Product ID	7TCG009520R0081
EAN	5414363067351
Catalog Description	CABLE TIE 40LB 6IN BLK NYL BLIND MT
Long Description	Blind Mounting Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, Length of 160mm (6.3 Inches), Width of 3.6mm (0.142 Inches), Thickness of 1.1mm (0.043 Inches), Tensile Strength Rating of 180 Newtons (40 Pounds)

Ordering

EAN	5414363067351
UPC	786210056401
Country of Origin	Hungary (HU)
Customs Tariff Number	3926909990
Selling Unit of Measure	each

Dimensions

Product Net Width	0.142 in 3.6 mm
Product Net Depth / Length	6.3 in 160 mm

Container Information

Package Level 1 Units	100 piece
Package Level 2 Units	500 piece
Package Level 2 Width	6.3 in 160 mm
Package Level 2 Height	3.5 in 89 mm
Package Level 2 Depth / Length	9.6 in 244 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Ty-Rap
Color	Black
Effective Date	19921009
Lock Type	Stainless Steel Barb
Material	Nylon/Polyamide 6.6
Product Name	TY-RAP FASTENING
Product Type	Blind Mounting
Tensile Strength	40 lb 180 N
Thickness	0.043 in 1.1 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TYG534MX
Instructions and Manuals	TYG534MX

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

