



PRODUCT-DETAILS

TYL300M

CABLE TIE 250LB 12IN NAT NYL RLSBLE



General Information

Extended Product Type	TYL300M
Product ID	7TCG054360R0353
EAN	5414363067542
Catalog Description	CABLE TIE 250LB 12IN NAT NYL RLSBLE
Long Description	Heavy Duty Releasable Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Releasable and Reusable, Length of 300mm (11.81 Inches), Width of 13.2mm (0.519 Inches), Tensile Strength Rating of 1120 Newtons (250 Pounds)

Ordering

EAN	5414363067542
UPC	786210549422
Country of Origin	Hungary (HU)
Customs Tariff Number	3926909990
Selling Unit of Measure	each

Dimensions

Product Net Width	0.519 in 13.2 mm
Product Net Depth / Length	11.81 in 300 mm

Container Information

Package Level 1 Units	50 piece
Package Level 2 Units	1000 piece
Package Level 2 Width	10.5 in 267 mm
Package Level 2 Height	13.75 in 349 mm
Package Level 2 Depth / Length	19.75 in 502 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Catamount
Bundle Diameter	2.95 in 75 mm
Color	Natural
Effective Date	19980621
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6
Product Name	CATAMOUNT FASTENING PRODUCTS
Product Type	Releaseable
Tensile Strength	50 lb 222 N

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TYL300M
Instructions and Manuals	TYL300M

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

