









Rating	10A 250VAC		Mounting Hole	
Contact Resistance	50m ohm Max.			
Insulation Resistance	DC 500V 100M ohm Min.			
Dielectric Strength	AC 1500V 1 minute			
Operation Temperature	-25°C~85°C			
Switch Function	4P DPST ON-OFF (NEON dependent)		Thickness:1.5~2.5	Thickness:0.7~2.5

Circuit Diagram



Frame: Black, Nylon 66
 Actuator: Yellow, PC
 Waterproof rubber: Black, Silicone
 Terminals: Silver plated, Copper alloy
 Printed: None
 Waterproof: IP65



Tolerances ± 0.3 Unless Otherwise Specified

Date	Name		Description					No.	
Drawn	Checked	Approved	SCI BOM No.	1826511	Model Name	ROCKER SWITCH			
曾敏捷		<i>Smau</i>	Customer No.		Model No.	R13-244B8-02		Rev.	0
08/16/17		8/18-17	Unit	mm	Shin Chin Industrial Co., Ltd.				