

7218G Water-repellent action nubuck ankle shoe

CE

EN ISO 20345 2011

S3 RS SRC ESD

ISO



- Upper**
Water-repellent Action nubuck with mesh insert and anti-abrasion reinforcement in toe cap area
- Outsole**
Single-density polyurethane
- Toe cap**
Polymer material, 200 joules
- Penetration-proof insole**
Composite fibre, ceramic treatment
- Underfoot cover**
Carbon, anatomically shaped
- Weight**
550
EU: 35-48 UK: 2.5-13
- Remarkably flexible and lightweight - approximate weight for size 42: 550 g
 - Not recommended for heavy-duty jobs (building, agriculture, heavy industry)

	art.	EU	UK	
072180135	7218G	35	2.5	228
072180136	7218G	36	3.5	235
072180137	7218G	37	4.5	242
072180138	7218G	38	5	248
072180139	7218G	39	6	255
072180140	7218G	40	6.5	262
072180141	7218G	41	7	268
072180142	7218G	42	8	275
072180143	7218G	43	9	282
072180144	7218G	44	10	288
072180145	7218G	45	10.5	295
072180146	7218G	46	11	302
072180147	7218G	47	12	308
072180148	7218G	48	13	315

7218G Water-repellent action nubuck ankle shoe

