

7246BK

Suede shoe, perforated

CE

EN ISO
20345
2011

S1P
SRC



- Upper
- Perforated suede
- Outsole
- Dual-density polyurethane
- Toe Cap
- Steel, 200 joules
- Penetration-proof insole
- Composite fibre, ceramic treatment
- Underfoot cover
- Felt carbon
- Weight
- 610
- EU: 35-48 UK: 2,5-13

	art.	EU	UK	
072461235	7246BK	35	2,5	228
072461236	7246BK	36	3,5	235
072461237	7246BK	37	4,5	242
072461238	7246BK	38	5	248
072461239	7246BK	39	6	255
072461240	7246BK	40	6,5	262
072461241	7246BK	41	7	268
072461242	7246BK	42	8	275
072461243	7246BK	43	9	282
072461244	7246BK	44	10	288
072461245	7246BK	45	10,5	295
072461246	7246BK	46	11	302
072461247	7246BK	47	12	308
072461248	7246BK	48	13	315

7246BK

Suede shoe, perforated

