

7382N Water resistant EXTREME 0-GRAVITY work shoes

CE **EN ISO 20345 2011** S3 SRC HRO WR



- Tomaia**
- Made from highly abrasion-resistant fabric
 - Inserts made from TPU (Thermoplastic polyurethane)
 - Heel stability support

- Outsole**
- EVA (Ethylene Vinyl Acetate)

- Toe cap**
- Polymer material, 200 joules

- Underfoot cover**
- EVA FOAM polyurethane cover with cushioning heel pad helping to prevent and alleviate pain in those who stand for long periods or walk much while working

Peso
550
EU: 38-48 UK: 5-13

	art.	EU	UK	
073820038	7382N	38	5	254
073820039	7382N	39	6	261
073820040	7382N	40	6,5	268
073820041	7382N	41	7	274
073820042	7382N	42	8	281
073820043	7382N	43	9	288
073820044	7382N	44	10	294
073820045	7382N	45	10,5	301
073820046	7382N	46	11	308
073820047	7382N	47	12	314
073820048	7382N	48	13	321

7382N Water resistant EXTREME 0-GRAVITY work shoes

