





DC Power Cable 0.5m long
PLUG 1.7x4.0 mm - straight
flexible, multiwire conductors,
stranded of bare copper wires
2x0.35mm²



Model	P40-TT-T035-050WH
DC Plug (output)	1.7x4.0mm, straight (round plug, outer diameter 4.0mm, inner diameter 1.7mm)
DC Socket (input)	tinned terminals
Construction	flexible, multiwire conductors, stranded of bare annealed copper wires
Cable cross section	1.6 x 3.4mm
Wire diameter	2x0.35mm²
Nominal voltage	0-100V
Rated current	0.8A
Length	50cm
Jacket	PVC
Color	White
Inner conductor	Cu
Insulation resistance	>100MΩ @ 500VDC
Insulation thickness	0.4mm
Allowable operation temperature	-20°C to 70°C
Maximum wire resistance	57.2 Ω/km @ 20°C



Marking System

model:

P40-TT-T035-050WH

1	2	3	4	5	6	7	8			
P	40	-	T	T	-	T	035	-	050	WH

1 Input / Output (side 1)

P - straight plug

A - angled plug

S - socket

2 Plug / Socket dimensions (side 1)

07 - 0.7mm / 2.35mm

13 - 1.3mm / 3.5mm

40 - 1.7mm / 4.0mm

48 - 1.7mm / 4.8mm

55 - 1.7mm / 5.5mm

21 - 2.1mm / 5.5mm

25 - 2.5mm / 5.5mm

3 Input / Output (side 2)

P - straight plug

A - angled plug

S - socket

4 Plug / Socket dimensions (side 2)

T - tinned terminals

07 - 0.7mm / 2.35mm

13 - 1.3mm / 3.5mm

40 - 1.7mm / 4.0mm

48 - 1.7mm / 4.8mm

55 - 1.7mm / 5.5mm

21 - 2.1mm / 5.5mm

25 - 2.5mm / 5.5mm

5 cable type

C- YTLYek (coaxial)

T- TLYP

O- YTLY

6 wire diameter

035 - 0.35mm²

050 - 0.5mm²

075 - 0.75mm²

100 - 1.0mm²

7 lenght

050 - 500mm

150 - 1500mm

8 color

BK - black

WH - white

TR - transparent