



TORCH 300 x 18 Tpi - 5 pcs

METAL: HEAVY DUTY TORCH™ DEMOLITION BLADES

- Strong: Robust 1.06 mm thick body.
- Shatter resistant: The bi-metal blade body will bend and flex but not break.
- Torch: - Thick 1.06 mm robust blade body for precise cuts in sheet metal and pipes.
- 25 mm blade height for improved stability and minimum vibration.



Article Number	48005789
Blade length (mm)	300
Material type	Bi-Met,Co
Max. cutting capacity inox (mm)	2 - 4
Max. cutting capacity metal pipe Ø (mm)	10 - 180
Max. cutting capacity non-ferrous metals (mm)	2 - 8
Max. cutting capacity steel (mm)	2 - 8
Max. cutting capacity wood with nails (mm)	No
Pack quantity	5