



# Shockwave HSS-G TiN Red Hex 4.8 mm - 1 pc

## RED HEX - SHOCKWAVE™ HSS-TIN METAL DRILL BITS

- Impact rated drill bit with 1/4" hex shank optimised for impact drivers.
- Titanium Nitride coating dispenses heat and makes the drill bit suitable for use also in high speed.
- QUAD EDGE™ Tip: unique combination of 135° split point and four cutting edges: 135° split point allows for precise & fast drilling start without walking. Four cutting edges create smaller chips to prevent heat build up for longer life.
- Variable flute geometry: For faster material ejection. Helps the bit run cooler and prevent it from burning out faster.
- Enhanced tapered web: Wider core towards the shank of the drill bit. Strengthens the core to increase overall flute durability.



|                     |          |
|---------------------|----------|
| Article Number      | 48894711 |
| Diameter (mm)       | 4.8      |
| Pack quantity       | 1        |
| Total length (mm)   | 78       |
| Working length (mm) | 29       |