



55 x 1.2 mm T 118 A - 5 pcs

TRADITIONAL BLADES

- Blade reference 4939274652 is especially suited to cutting very thin sheet material because of its low 0.7 mm tooth pitch.
- For those professionals desiring extra lifetime and durability we recommend the use of Bi-Metal blades in conjunction with a suitable cooling lubricant, the blades lifetime is double that of non Bi-Metal blades.



Article Number	4932254063
Blade length (mm)	55
Max. cutting capacity aluminium (mm)	-
Max. cutting capacity inox (mm)	-
Max. cutting capacity non-ferrous metals (mm)	1.5 - 4
Max. cutting capacity perspex (mm)	-
Max. cutting capacity PVC (mm)	-
Max. cutting capacity sandwich material (mm)	-