



HSSR Set - 25 pcs

METAL DRILL BITS HSS ROLLFORGED - DIN 338 - CASSETTES

- High speed steel rollforged metal drill bits produced according to DIN 338.
- Oxide coating enables quick swarf removal.
- Normal point shaped cutting tip with 118° angle.
- Type N flute normal angle.
- Suitable for drilling in steel, cast iron, alloyed and non-alloyed material up to 800 N/mm².
- Colour: black.



Article Number	4932352469
Contents	1 / 1.5 / 2 / 2.5 / 3 / 3.5 / 4 / 4.5 / 5 / 5.5 / 6 / 6.5 / 7 / 7.5 / 8 / 8.5 / 9 / 9.5 / 10 / 10.5 / 11 / 11.5 / 12 / 12.5 / 13 mm
Pack quantity	25
Supplied in	Metal case