



# VDE Long Round Nose Pliers 205mm

## VDE ROUND NOSE PLIERS

- VDE (DIN EN/IEC 60900) certified tools. Tested to 10,000 volts and guaranteed to 1,000 volts. Tested against cold to -40°.
- Steel blades are fully forged, hardened and tempered for best durability. Grey titanium surface finish is non reflective and ensures maximum corrosion resistance.
- Induction hardened cutting edges to cut even the hardest of materials.
- Precision machined joint for maximum power transmission with optimum leverage for easy and effortless work.
- Ergonomic grip with softgrip for comfortable handling and good grip.



|                                                                    |            |
|--------------------------------------------------------------------|------------|
| Article Number                                                     | 4932464564 |
| Capacity (mm)                                                      | -          |
| Capacity pipe [Max. mm]                                            | -          |
| Cutting capacity in cable Al and Cu (Max. Ø mm)                    | -          |
| Cutting capacity in hard wire 1800N/mm <sup>2</sup> (Max. mm)      | 2.2        |
| Cutting capacity in soft wire 220N/mm <sup>2</sup> (Max. mm)       | 3.9        |
| Cutting capacity in very hard wire 2300N/mm <sup>2</sup> (Max. mm) | -          |
| Length (mm)                                                        | 205        |
| Pack quantity                                                      | 1          |