

Flat suction cup (round)

SUF 60 SI-55 M10x1.25-IG N009

Part no...:10.01.01.13975

<https://www.schmalz.com/10.01.01.13975>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups SUF > SUF 60 SI-55 M10x1.25-IG N009

Flat suction cup (round) f. process- safe handling of smooth or slightly rough surfaces



Size: 60

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible

Design Data



Attribute	Value
Dmax(S)	66.40 mm
Ds	60 mm
G1	M10x1.25-F
H	17 mm
LG1	6 mm
Z (Stroke)	5.50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	140 N
Pull-off force	140 N
Volume	12.70 cm ³
Curve radius (min) (convex)	75 mm
Hose diameter (empf.) d	6 mm
Size	60
Suction cup material	Silicone SI
Material hardness [Shore A]	55 Shore A

Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Flat suction cup (round)

SUF 60 SI-55 M10x1.25-IG N009

Part no...:10.01.01.13975

<https://www.schmalz.com/10.01.01.13975>

Weight	31 g
Product family	SUF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



TVN G1/4-AG 9 N009

Part no...:10.05.10.00065

Thread G1: G1/4"-M

Thread G2: M10x1.25-M

Spring stroke Z: 9 mm

Nipple: N 009