

Flat suction cup (round)

SUF 40 HT1-60 SC050

Part no...:10.01.01.13995

<https://www.schmalz.com/10.01.01.13995>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > SUF 40 HT1-60 SC050

Flat suction cup (round) f. process- safe handling of smooth or slightly rough surfaces




Size: 40

Suction cup material: High temp material HT1

Material hardness [Shore A]: 60 Shore A

Design Data



Attribute	Value
d1	17.20 mm
d	11 mm
Dk	24.80 mm
Dmax(S)	44 mm
Ds	40 mm
H	16 mm
H2	6.80 mm
H3	9.30 mm
Z (Stroke)	4 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	61 N
Pull-off force	61 N
Volume	3.80 cm ³
Curve radius (min) (convex)	50 mm
Size	40
Nipple family	SC050
Suction cup material	High temp material HT1
Material hardness [Shore A]	60 Shore A
Weight	8.50 g

Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Flat suction cup (round)

SUF 40 HT1-60 SC050

Part no.:10.01.01.13995

<https://www.schmalz.com/10.01.01.13995>

Product family

SUF

Accessories



SC 050 G1/8-AG

Part no.:10.01.06.04250

Connection geometry: 050

Vacuum connection: G1/8"-M

Fitting length: 7.2 mm

Nominal diameter dn: 4.1 mm



SC 050 G1/8-IG

Part no.:10.01.06.04308

Connection geometry: 050

Vacuum connection: G1/8"-F

Fitting length: 14 mm

Nominal diameter dn: 6.1 mm

Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl