

Open End Wrench & Set

1900

- European slimline type
- 15° open end angle
- Chrome vanadium alloy steel
- Chrome plated
- Metric - DIN 3110
- Inch - ANSI / ASME B107.6



5900



KT NO.	Size mm	L mm		
19005507	5.5 x 7	123	20	12 / 576
19000607	6 x 7	123	23	12 / 576
19000708	7 x 8	140	33	12 / 576
19000809	8 x 9	140	32	12 / 576
19000810	8 x 10	140	33	12 / 576
19000911	9 x 11	156	56	12 / 288
19001011	10 x 11	156	46	12 / 288
19001012	10 x 12	156	45	12 / 288
19001113	11 x 13	172	65	12 / 288
19001213	12 x 13	172	80	12 / 288
19001214	12 x 14	172	64	12 / 288
19001314	13 x 14	172	81	12 / 288
19001317	13 x 17	195	104	12 / 192
19001415	14 x 15	188.5	89	12 / 192
19001417	14 x 17	195	106	12 / 192
19001617	16 x 17	204	122	12 / 192
19001618	16 x 18	221	158	12 / 144
19001719	17 x 19	221	158	12 / 144
19001819	18 x 19	221	160	12 / 144
19001921	19 x 21	237	207	12 / 144
19001922	19 x 22	237	203	12 / 144
19002022	20 x 22	237	209	12 / 144
19002123	21 x 23	247	241	6 / 72
19002224	22 x 24	247	235	6 / 72
19002326	23 x 26	263	305	6 / 72
19002426	24 x 26	263	295	6 / 72
19002427	24 x 27	263	301	6 / 72

KT NO.	Size mm	L mm		
19002430	24 x 30	263	306	6 / 72
19002528	25 x 28	279	348	6 / 48
19002632	26 x 32	285	438	6 / 48
19002729	27 x 29	279	348	6 / 48
19002730	27 x 30	285	431	6 / 48
19002732	27 x 32	285	434	6 / 48
19003032	30 x 32	298	439	6 / 48
19003036	30 x 36	351	715	6 / 36
19003236	32 x 36	351	723	5 / 30
19003436	34 x 36	351	717	5 / 30
19003641	36 x 41	380	998	4 / 24
19004146	41 x 46	430	1337	4 / 16

KT NO.	Size inch	L mm		
59000810	1/4 x 5/16	123	23	12 / 576
59001012	5/16 x 3/8	140	32	12 / 576
59001214	3/8 x 7/16	156	45	12 / 288
59001416	7/16 x 1/2	172	69	12 / 288
59001618	1/2 x 9/16	172	70	12 / 288
59001820	9/16 x 5/8	188.5	88	12 / 192
59002022	5/8 x 11/16	204	120	12 / 192
59002224	11/16 x 3/4	221	163	12 / 144
59002628	13/16 x 7/8	237	202	12 / 144
59003032	15/16 x 1	247	311	6 / 72
59003034	15/16 x 1-1/16	263	304	6 / 72
59003236	1 x 1-1/8	279	341	6 / 48
59003640	1-1/8 x 1-1/4	298	431	6 / 48



► MRN / SRN : Teton pouch bag



► MR / SR : Nylon pouch bag

KT NO.	PC.	Contents	Package		
1106MR	6	8 x 9, 10 x 12, 12 x 14, 14 x 17, 17 x 19, 21 x 23	Nylon	0.83	1 / 24
1106MR01	6	8 x 9, 10 x 11, 12 x 13, 14 x 15, 16 x 17, 18 x 19	Nylon	0.81	1 / 24
1108MR	8	6 x 7, 8 x 9, 10 x 11, 12 x 13, 14 x 15, 16 x 17, 18 x 19, 20 x 22	Nylon	0.91	1 / 24
1110MR	10	6 x 7, 8 x 9, 10 x 11, 12 x 13, 14 x 15, 16 x 17, 18 x 19, 20 x 22, 24 x 27, 25 x 28	Nylon	1.67	1 / 16
1112MR	12	6 x 7, 8 x 9, 10 x 11, 12 x 13, 14 x 15, 16 x 17, 18 x 19, 20 x 22, 21 x 23, 24 x 27, 25 x 28, 30 x 32	Nylon	2.37	1 / 10
1112MRN	12		Teton	2.45	
1108SR	8	1/4 x 5/16, 5/16 x 3/8, 3/8 x 7/16, 7/16 x 1/2, 9/16 x 5/8, 5/8 x 11/16, 11/16 x 3/4, 13/16 x 7/8	Nylon	0.91	1 / 24
1110SR	10	1/4 x 5/16, 5/16 x 3/8, 3/8 x 7/16, 7/16 x 1/2, 9/16 x 5/8, 5/8 x 11/16, 11/16 x 3/4, 13/16 x 7/8, 15/16 x 1-1/16, 1 x 1-1/8	Nylon	1.67	1 / 16
1112SR	12	1/4 x 5/16, 5/16 x 3/8, 3/8 x 7/16, 7/16 x 1/2, 9/16 x 5/8, 5/8 x 11/16, 11/16 x 3/4, 13/16 x 7/8, 15/16 x 1, 15/16 x 1-1/16, 1 x 1-1/8, 1-1/8 x 1-1/4	Nylon	2.5	1 / 10