

Marking Punch



CAUTION Please wear proper safety gear while working.



11409SQ

- Chrome vanadium alloy steel
- Hardened and tempered control HRC60 for safe use
- Invert number 6 to be number 9 (For 11409SQ)
- The letter A~Z with extra "&" (ampersand) included (For 11427SQ)

11427SQ



KT NO.	Font size mm	Font size Inch	Contents	Shank mm ²	L mm	Kg	Box / Carton
11409SQ02	2.0	5/64"	9 PCS 0~9	6.35	61	0.18	1 / 120
11409SQ03	3.0	1/8"		6.35	61	0.18	1 / 120
11409SQ04	4.0	5/32"		6.35	59	0.18	1 / 120
11409SQ05	5.0	3/16"		8	61	0.28	1 / 80
11409SQ06	6.0	1/4"		9.53	61	0.43	1 / 60
11409SQ08	8.0	5/16"		12.7	71	0.78	1 / 30
11427SQ02	2.0	5/64"	27 PCS A~Z, &	6.35	61	0.52	1 / 50
11427SQ03	3.0	1/8"		6.35	61	0.52	1 / 50
11427SQ04	4.0	5/32"		6.35	59	0.52	1 / 50
11427SQ05	5.0	3/16"		8	61	0.82	1 / 30
11427SQ06	6.0	1/4"		9.53	61	1.25	1 / 20
11427SQ08	8.0	5/16"		12.7	71	2.33	1 / 10

Heavy Duty Marking Punch

11509SQ

- Chrome vanadium alloy steel
- Hardened and tempered control HRC60 for safe use
- Hardness reduced at striking end HRC40 to have longer life time
- Invert number 6 to be number 9 (For 11509SQ)
- The letter A~Z with extra "&" (ampersand) included (For 11527SQ)

11527SQ



KT NO.	Font size mm	Font size Inch	Contents	Shank mm ²	L mm	Kg	Box / Carton
11509SQ05	5.0	3/16"	9 PCS 0~9	11	61	0.56	1 / 30
11527SQ05	5.0	3/16"	27 PCS A~Z, &	11	61	1.70	1 / 10

