

# Socket Set

2526MR

Metal case size (mm) :  
244 x 118 x 37 (0.038 cuft)



2526MR

2526SR

1/4"



2526SR

26  
PC.

| KT NO. | Contents |                                                                 | Kg 1.30 1 / 18 |                    |
|--------|----------|-----------------------------------------------------------------|----------------|--------------------|
| 2526MR | 2335M    | 4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 13                          | 2779-55G       | 2221-02<br>2221-04 |
|        | 2235M    | 4, 5, 5.5, 6, 7, 8, 9, 10, 11, 13                               |                |                    |
| 2526SR | 2335S    | 5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 15/32, 1/2 | 2792           | 2813               |
|        | 2235S    | 5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2        |                |                    |

2031MR

Metal case size (mm) :  
280 x 130 x 41 (0.053 cuft)

| KT NO. | Contents |                                       | Kg 1.60 1 / 15                               |                                |
|--------|----------|---------------------------------------|----------------------------------------------|--------------------------------|
| 2031MR | 2330M    | 4, 4.5, 5, 6, 7, 8, 9, 10, 11, 12, 13 | T8, T9, T10, T15, 2033<br>T20, T25, T27, T30 | 2779-55G<br>2221-03<br>2221-06 |
| 2531MR | 2335M    |                                       | H3, H4, H5, H6, 2035<br>H8, H10              | 2179DF<br>2571-45<br>2792      |

2531MR

1/4"



31  
PC.

2030CR

Metal case size (mm) :  
244 x 118 x 37 (0.038 cuft)



30  
PC.

2530CR 1/4"

| KT NO. | Contents |                                                          | Kg 1.30 1 / 18   |                     |
|--------|----------|----------------------------------------------------------|------------------|---------------------|
| 2030CR | 2330M    | 4, 4.5, 5, 6, 7, 8, 9, 10, 11, 12                        | 2310M<br>8, 10   | 2310S<br>5/16, 3/8  |
|        | 2330S    | 5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2 |                  |                     |
| 2530CR | 2335M    | 4, 4.5, 5, 6, 7, 8, 9, 10, 11, 12                        | 2769-55F<br>2792 | 2571-45<br>2452-05F |
|        | 2335S    | 5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2 |                  |                     |

2539MR

Metal case size (mm) :  
280 x 130 x 41 (0.053 cuft)



39  
PC.

| Contents |                                            | Kg 1.61 1 / 15     |                             |
|----------|--------------------------------------------|--------------------|-----------------------------|
| 2335M    | 4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13 | 2375M              | E4, E5, E6, E7, E8          |
| 2375M    |                                            |                    |                             |
| 2033     | T8, T9, T10, T15, T20, T25, T27, T30, T40  | 2035               | H3, H4, H5, H6, H7, H8, H10 |
| 2035     |                                            |                    |                             |
| 2779-55G |                                            | 2179DF             |                             |
| 2571-45  |                                            |                    |                             |
|          |                                            | 2221-02<br>2221-04 | 2792                        |