

L- type Wrench Set



► Tray



► Shelf

KT NO.	PC.	Spec	Contents	Package		
22106MR	6	Ball & hex two way type	1160MR H3, H4, H5, H6, H7, H8	Tray	0.68	1 / 20
22108MR	8		1160MR H2, H2.5, H3, H4, H5, H6, H8, H10	Tray	0.97	1 / 10
22208MR	8	Hex head	1165MR H2, H2.5, H3, H4, H5, H6, H8, H10	Tray	0.97	1 / 10
22306TR	6	torx head	1163TR T10, T15, T20, T25, T30, T40	Tray	0.46	1 / 20
22309TR	9		1163TR T10, T15, T20, T25, T27, T30, T40, T45, T50	Tray	1.00	1 / 10
22118MR	8	Ball & hex two way type	1160MR H2, H2.5, H3, H4, H5, H6, H8, H10	Shelf	1.10	1 / 12
22218MR	8	Hex head	1165MR H2, H2.5, H3, H4, H5, H6, H8, H10	Shelf	1.10	1 / 12
22319TR	9	torx head	1163TR T10, T15, T20, T25, T27, T30, T40, T45, T50	Shelf	1.12	1 / 12


T - type Wrench

- Material - SNCM - V alloy steel
- Finishing - chrome plated with black tip

1150MR



- Hexagon with ball point head



1155MR

- Hexagon head

1155SR



KT NO.						
115002MR	H2	100	137	90	28	10 / 200
115025MR	H2.5	100	137	90	30	10 / 200
115003MR	H3	100	137	90	32	10 / 200
115004MR	H4	100	137	90	38	10 / 200
115005MR	H5	150	188	100	65	10 / 200
115006MR	H6	150	188	100	79	10 / 200
115008MR	H8	200	240	120	159	10 / 120
115010MR	H10	200	240	120	217	10 / 120

KT NO.						
115502MR	H2	100	137	90	28	10 / 200
115525MR	H2.5	100	137	90	30	10 / 200
115503MR	H3	100	137	90	32	10 / 200
115504MR	H4	100	137	90	38	10 / 200
115505MR	H5	150	188	100	65	10 / 200
115506MR	H6	150	188	100	79	10 / 200
115508MR	H8	200	240	120	159	10 / 120
115510MR	H10	200	240	120	217	10 / 120
115525SR	5/64	100	137	90	19	10 / 200
115503SR	3/32	100	137	90	21	10 / 200
115504SR	1/8	100	137	90	25	10 / 200
115505SR	5/32	100	137	90	30	10 / 200
115506SR	3/16	150	188	100	56	10 / 200
115508SR	1/4	150	188	100	78	10 / 200
115510SR	5/16	200	240	120	158	10 / 120
115512SR	3/8	200	240	120	202	10 / 120

