

Socket Set

2540MR

1/4"

Metal case size (mm):
316 x 104 x 40 (0.047 cuft)



39
PC.

Contents



1.52 1 / 12

2335M	4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13
1025S	4, 5.5, 7
1025P	PH0, PH1, PH2, PH3
1025H	H3, H4, H5, H6, H7, H8
1025T	T10, T15, T20, T25, T30, T40
2779-55G	213312DF
2571-45	2452-05F
	2221-02
	2221-06

2575MR

1/4"

Metal case size (mm):
244 x 118 x 37 (0.038 cuft)



45
PC.

Contents



1.24 1 / 18

2335M	4, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13, 14
1025S	4, 6.5, 7, 8
1025P	PH1, PH2, PH3
1025H	H2.5, H3, H4, H5, H6, H7, H8, H10
1025U	T8H, T9H, T10H, T15H, T20H, T25H, T27H, T30H, T40H
1025Z	PZ1, PZ2, PZ3
2755-55G	2223-02
2311-06	2179DF
	2142

2551MR

Metal case size (mm):
244 x 118 x 37 (0.038 cuft)



2551MR

2551MR01

1/4"



51
PC.

KT NO.

Contents



1.30 1 / 18

2551MR	2755-55G	2335M	4, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13, 14	1025U	T10H, T15H, T20H, T25H, T27H, T30H, T40H	2813	2142	2792
		1025S	3, 4, 5, 6	1025Z	PZ1, PZ2 x2, PZ3	7702-25		753-63
2551MR01	2761-55F	1025P	PH1, PH2 x2, PH3	1025T	T10, T15, T20, T25, T27, T30, T40	2223-02		2178DF
		1025H	H3, H4, H5, H6			2223-04		

2516MRV03

Plastic case size (mm) :
199 x 161 x 56 (0.063 Cuft)

Tray category #11 (187 x 140mm) 1/4"

Contents



0.75 1 / 16

2335M	4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13, 14
2771-55G	2571-45
2221-06	2792



17
PC.

2524MRV

Plastic case size (mm) :
199 x 161 x 56 (0.063 Cuft)

Tray category #11 (187 x 140mm) 1/4"

Contents



0.9 1 / 16

2335M	4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13, 14
2771-55G	2571-45
2221-02	2142
2221-04	2178DF
2221-06	2792



21
PC.