

Accessory

KT No. & D1

2453

1/4"

- Flexible handle
- Action degree -180°
- New pattern design added in firm and powerful elements
- New forge technologies I-Beam shank offers 15% lightweight
- DIN 3122



2452DK

KT NO.	Overall length inch	mm		
2453-05F	5	130	71	15 / 270
2452DK	renewal kits			

- Material - chrome vanadium alloy steel
- Finishing - polished, chrome plated & black phosphate sunk

2571

1/4"

- Sliding T-handle
- DIN 3122



KT NO.	Overall length inch	mm		
2571-45	4-1/2	115	44	12 / 192

KT No. & D1

2141

2142

1/4"

- Bit holder
- DIN 3122



2141



2142

KT NO.	Size inch	Overall length mm		
2141	1/4	25	14.0	20 / 320
2142	1/4	25	15	20 / 320

Socket Rail Set

2509MR

1/4"

- Socket rail 150mmL

9
PC.

Contents			
2335M	4, 5, 6, 7, 8, 9, 10, 11, 13	0.17	40
8720609			

Socket Rail Set

2509SR

1/4"

- Socket rail 150mmL

9
PC.

Contents			
2335S	5/32, 3/16, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2	0.17	40
8720609			

2513MR

1/4"

- Socket rail 240 mmL

13
PC.

Contents			
2335M	4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13, 14	0.23	6 / 60
8721114			

2513MRD1

1/4"

- Socket rail 508 mmL

13
PC.

Contents			
2335M	4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13, 14	0.34	50
8720813D1			

2311MR

1/4"

- Socket rail 240 mmL

13
PC.

Contents			
2235M	4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13, 14	0.46	6 / 60
8721114			

2127PR

1/4"

- Socket rail 130mmL
- For hex head screw
- H : 37mm

7
PC.

Contents			
2035	H3, H4, H5, H6, H7, H8, H10	0.15	50
8720507			