

Socket Set

3023MR

Metal case size (mm) :
372 x 153 x 40 (0.08 cuft)

KT NO.	Contents		2.8	1 / 6
3023MR	3330M	6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 19, 20, 21, 22	3769-08F	3452-08F 3571-08
3523MR	3335M			3221-03 3221-06 3792



22 PC.

3024MR

Metal case size (mm) :
318 x 147 x 46 (0.076 cuft)

KT NO.	Contents		2.2	1 / 10
3024MR	3330M	6, 7, 8, 9, 10, 11, 13, 14, 17, 19	3021	PH2, PH3
3524MR	3335M		3022	5, 8
3024SR	3330S		3025	H3, H4, H5, H6, H7, H8, H10
		1/4, 5/16, 11/32, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4	3779-08G 3792	3221-06



3024MR/3524MR

24 PC.



3024SR

3027MR

Metal case size (mm) :
318 x 147 x 46 (0.076 cuft)

KT NO.	Contents		2.6	1 / 10
3027MR	3330M	7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19	3235M	3779-08G
3527MR	3335M			3221-03
3027SR	3330S	1/4, 5/16, 11/32, 3/8, 7/16, 15/32, 1/2, 9/16, 19/32, 5/8, 11/16, 3/4, 13/16		3812
	3235S	5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16		3792



3027MR/3527MR

26 PC.



3027SR

3034MR

Metal case size (mm) :
372 x 153 x 40 (0.08 cuft)

KT NO.	Contents		3.1	1 / 6
3034MR	3330M	6, 7, 8, 9, 10, 11, 13, 14, 17, 19	3375M	E4, E5, E6, E7, E8, E10, E12, E14, E16, E18
			3023	T8, T9, T10, T15, T20, T25, T27, T30, T40, T45
3534MR	3335M		3779-08G	3452-10F
			3571-08	3221-03 3221-06 3792

3534MR

3/8"



36 PC.