

Accessory

KT No. & D1



3792

3/8"

- Universal joint
- DIN 3123




KT NO.	Overall length Inch	mm		
3792	2	50	67	15 / 300

3794

3/8"

- Universal joint
- 30° rotation
- Short pattern design enables greater access in confined spaces



KT NO.	Overall length Inch	mm		
3794	1-4/5	46	106	15 / 300

3812

3814

3/8"

- Adapter
- Convert to 1/4" drive or 1/2" drive
- 3812 → Max. torque : 62 N·m
- DIN 3123, ISO 3316

1/4" drive (M) 3/8" drive (F)
1/2" drive (M)



3812 / 3814

KT NO.	Spec.		
3812	3/8"Fx1/4"M	30	12 / 192
3814	3/8"Fx1/2"M	46	12 / 360

3148

3/8"

- Bit holder
- DIN 3120 / 3126



KT NO.	Size	Overall length mm		
314808S	1/4"	30	35	12 / 360
314810S	5/16"	30	35	12 / 360
314810M	10 mm	30	35	12 / 360

Socket Rail Set

3013MR

3013SR

3513MR

3/8"

- Socket rail 290mmL

13
PC.

KT NO.	Contents	0.52	35
3013MR	3330M 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19	8731213	
3013SR	3330S 1/4, 5/16, 11/32, 3/8, 7/16, 15/32, 1/2, 9/16, 19/32, 5/8, 11/16, 3/4, 13/16		
3513MR	3335M 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19		

3508MR10

3/8"

- Socket rail 210mmL

8
PC.

Contents	0.65	24
3235M 10, 11, 12, 13, 14, 16, 17, 19 8730808		

3106PR

3/8"

- Socket rail 150mmL

6
PC.

Contents	0.28	40
3375M E8, E10, E12, E14, E16, E18 8730606		

3116PR

3/8"

- Socket rail 150mmL

6
PC.

Contents	0.39	50
3275M E4, E5, E8, E10, E12, E14 8730606		

3129PR

3/8"

- Socket rail 210mmL

9
PC.

Contents	0.27	40
3375M E4, E5, E6, E7, E8, E10, E12, E14, E16 8730809		