

Standard Socket

3335VE

3/8"

IEC 60900:2012



KT NO.	mm	L mm		
3335VE06M	6	44.5	25	5 / 45
3335VE07M	7	44.5	26	5 / 45
3335VE08M	8	44.5	27	5 / 45
3335VE09M	9	44.5	27	5 / 45
3335VE10M	10	44.5	28	5 / 45
3335VE11M	11	44.5	29	5 / 45
3335VE12M	12	44.5	29	5 / 45
3335VE13M	13	44.5	32	5 / 45
3335VE14M	14	44.5	35	5 / 45
3335VE15M	15	46	40	5 / 45
3335VE16M	16	46	42	5 / 45
3335VE17M	17	46	47	5 / 45
3335VE18M	18	46	48	5 / 60
3335VE19M	19	46	51	5 / 60
3335VE20M	20	46	55	5 / 60
3335VE21M	21	46	59	5 / 60
3335VE22M	22	46	63	5 / 60
3335VE24M	24	46	66	5 / 60

Deep Socket

3235VE

3/8"

IEC 60900:2012



KT NO.	mm	L mm		
3235VE08M	8	79	52	5 / 50
3235VE10M	10	79	60	5 / 50
3235VE12M	12	79	68	5 / 50
3235VE14M	14	79	76	5 / 50

Insulated Tool Set

35VE01MRV

3/8"

IEC 60900:2012

Handy case size (mm) :
389 x 229 x 66 (1.49cuft)

Contents

2.16 1 / 6

3335VE	10, 11, 12, 13, 14, 17, 19
3025VE	5, 6, 8,
3221VE	6, 10,
3771VE-08	3178VE-08

Bit Socket

3025VE

3/8"

IEC 60900:2012



KT NO.	mm	Overall length mm		
3025VE04	H4	65	37	5 / 50
3025VE05	H5	65	38	5 / 50
3025VE06	H6	65	39	5 / 50
3025VE08	H8	65	42	5 / 50
3025VE10	H10	65	51	5 / 50

Ratchet

3771VE

3/8"

IEC 60900:2012



KT NO.	Overall length mm		
3771VE-08	200	300	2 / 20

Accessory

3221VE

3/8"

IEC 60900:2012



KT NO.	Overall length mm		
3221VE-06	150	150	4 / 48
3221VE-10	250	250	4 / 24

3178VE

3/8"

IEC 60900:2012



KT NO.	mm		
3178VE-08	200	240	2 / 12



14 PC.