

## Bit Socket Set

**4109PR**

 Metal case size (mm) :  
198 x 105 x 32 (0.023 cuft)

**9  
PC.**


4109PR



4119PR

| KT NO. | Contents |                                             |      |        |
|--------|----------|---------------------------------------------|------|--------|
| 4109PR | 4023     | T20, T25, T27, T30, T40, T45, T50, T55, T60 | 1.04 | 1 / 20 |
| 4119PR | 4033     |                                             | 1.13 | 1 / 20 |

**4110PR**

 Metal case size (mm) :  
198 x 105 x 32 (0.023 cuft)

**9  
PC.**


4110PR



4120PR

| KT NO. | Contents |                                        |      |        |
|--------|----------|----------------------------------------|------|--------|
| 4110PR | 4025     | H3, H4, H5, H6, H7, H8, H10, H12, H14  | 1.03 | 1 / 20 |
| 4120PR | 4035     | H4, H5, H6, H7, H8, H10, H12, H14, H17 | 1.38 | 1 / 20 |

**4117PR**

 Metal case size (mm) :  
224 x 94 x 40 (0.03 cuft)

**7  
PC.**


| Contents                   |      |       |
|----------------------------|------|-------|
| 4026 M6, M8, M10, M12, M14 | 1.22 | 1 / 8 |
| 402B M16, M18              |      |       |

**4128PR**

 Metal case size (mm) :  
224 x 94 x 40 (0.03 cuft)

**8  
PC.**


| Contents             |      |       |
|----------------------|------|-------|
| 4026 M5, M6, M8, M10 | 1.24 | 1 / 8 |
| 402B M16             |      |       |
| 4036 M8, M10, M12    |      |       |

## Socket Set

**4501MR**

 Metal case size (mm) :  
392 x 90 x 50 (0.062 cuft)

**15  
PC.**


| Contents                                             |      |       |
|------------------------------------------------------|------|-------|
| 4335MR 8, 10, 11, 12, 13, 14, 17, 19, 21, 22, 24, 27 | 3.28 | 1 / 6 |
| 4779-10FR  4251-05R                                  |      |       |
| 4452-15FR                                            |      |       |

**4511MR**

 Metal case size (mm) :  
445 x 187 x 50 (0.147 cuft)

**24  
PC.**


4511MR



4511SR

| KT NO. | Contents                                                                                                              |     |       |
|--------|-----------------------------------------------------------------------------------------------------------------------|-----|-------|
| 4511MR | 4335MR 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24, 27, 30, 32                                         | 5.5 | 1 / 4 |
| 4511SR | 4335SR 3/8, 7/16, 15/32, 1/2, 9/16, 19/32, 5/8, 11/16, 3/4, 25/32, 13/16, 7/8, 15/16, 1, 1-1/16, 1-1/8, 1-3/16, 1-1/4 |     |       |
|        | 463521RC  4725-12GR  4572-10  4251-05R  4251-10R  4223-02R                                                            |     |       |