

Impact Accessory & Set

4269

1/2"

- Torque extension bar
- Color coded and engraved with N-m and lbf-ft setting
- Helps to eliminate overtightened lug nut


KT NO.	Color	Max. torq N·m	Max. torq lbf·ft	Overall length inch	Overall length mm	
4269-08-90	Green	90	65	7-11/16	195	192
4269-08-A0	Black	100	75	7-11/16	195	201
4269-08-B0	Yellow	110	80	7-11/16	195	217
4269-08-C0	Red	120	90	7-11/16	195	224
4269-08-D5	Blue	135	100	7-11/16	195	238
4269-08-F0	Orange	150	110	7-11/16	195	263
4269-08-G0	Grey	160	120	7-11/16	195	304
4269-08-H5	Brown	175	130	7-11/16	195	284
4269-08-J0	White	190	140	7-11/16	195	331
4269-08-K0	Light Blue	200	150	7-11/16	195	344



How to use torque extension bar

1. Use with 1/2" DR. impact wrench, don't use by hand.
2. Set air pressure 0.6 MPa(90 PSI) and adjust torque value between 190 N·m and 210 N·m.
3. Select suitable torque extension bar according to wheel nut size and indicated tightening torque.
4. Attach the torque extension bar with socket to impact wrench and apply load.
5. Check the actual tightening torque value by torque wrench.
6. Adjust air pressure or torque value according to the result of above.
7. Tight other wheel nuts in diagonal order.

Torque(N·m)



Standard impact socket

90N-m Torque extension bar

1/2" Impact wrench
0.6Mpa Air pressure

4481PP1

1/2"

- Torque extension bar set


Contents		2.58	1 / 6
	4269-08-90	90 N·m	
	4269-08-A0	100 N·m	
	4269-08-B0	110 N·m	
	4269-08-C0	120 N·m	
	4269-08-D5	135 N·m	
	4269-08-F0	150 N·m	
	4269-08-G0	160 N·m	
	4269-08-H5	175 N·m	
	4269-08-J0	190 N·m	
	4269-08-K0	200 N·m	



10
PC.

9TE41

- Hook for torque extension bar
- Groove capacity : 22 mm



KT NO.	Overall length (mm)		
9TE41	311	196.4	1 / 24