



4462

1/2"

- Flexible handle
- Action degree -180°
- DIN 3122



KT NO.	Overall length inch	Overall length mm		
4462-18F	18	463	1046	1 / 20
4462-24F	24	613	1350	1 / 20
4462DK	renewal kits		-	-

4572

1/2"

- Sliding T-handle
- DIN 3122



KT NO.	Overall length inch	Overall length mm		
4572-10	10	250	371	2 / 40
4572-12	12	300	426	2 / 40
4572DK	renewal kits		-	-

4573

1/2"

- Sliding T-handle
- DIN 3120



KT NO.	Overall length inch	Overall length mm		
4573-10R	10	250	470	2 / 40
4573DK	renewal kits		-	-

4581

1/2"

- 90° L-handle
- DIN 3122



KT NO.	Overall length inch	Overall length mm		
4581-10	10	250	450	1 / 40

4583

1/2"

- 105° L-handle
- DIN 3120




KT NO.	Overall length inch	Overall length mm		
4583-12R	12-1/2	315	550	1 / 40

4584

1/2"

- 90° L-handle
- DIN 3120



KT NO.	Overall length inch	Overall length mm		
4584-12R	12	300	547	40

4791R

1/2"

- Univesal joint
- DIN 3120, ISO 3316



KT NO.	Overall length inch	Overall length mm		
4791R	3	77.5	159	5 / 100

4794

1/2"

- Univesal joint
- 30° rotation
- Short pattern design enables greater access in confined spaces



KT NO.	Overall length inch	Overall length mm		
4794	2-3/8	60	105	5 / 180

4813

4816

1/2"

- Adapter
- Convert to 3/8" drive or 3/4" drive
- 4813 → Max. torque : 202 N-m
- DIN 3123, ISO 3316



KT NO.	Spec.			
4813	3/8" drive(M)	56	10 / 200	
4816	3/4" drive(M)	111	10 / 200	

4148

1/2"

- Bit holder



KT NO.	Size	Overall length mm		
414808S	1/4"	38	50	10 / 200
414810S	5/16"	38	55	10 / 200
414810M	10 mm	38	56	10 / 200