

Accessory

6572

3/4"

- Sliding T-handle
- DIN 3122



KT NO.

Overall length
inch mm

6572-20	20	500	1542	1 / 10
6572DK	renewal kits		-	-

6581

3/4"

- 90° L-handle



KT NO.

Overall length
inch mm

6581-12	12	300	1307	10
6581-18	18	450	1939	12

6585

3/4"

- Double driver L-handle 90°



KT NO.

Overall length
inch mm

6585-19	19	478	2010	12
---------	----	-----	------	----

6791

3/4"

- Universal joint
- DIN 3123, ISO 3316



KT No. & D1

KT NO.

Overall length
inch mm

6791	4-1/4	108	571	2 / 20
------	-------	-----	-----	--------

6814

6818

3/4"

- Adapter
- Convert to 1/2" drive or 1" drive
- 6814→Max. torque : 512 N·m
- DIN 3123, ISO 3316

KT No. & D1

1/2" drive(M)
1" drive(M)

3/4" drive(F)

6814 / 6818

KT NO.

Spec.



6814	3/4"F x 1/2"M	120	8 / 96
6818	3/4"F x 1"M	296	6 / 60

Socket Rail

8760807D1

3/4"

- Socket rail carrier with retaining clip
- 26" roller cabinet



KT NO.

Square
drive

Clip

L
(mm)

8760807D1	3/4"	7	508
8760			

Socket Set

6014MR

Metal case size (mm) :
537 x 177 x 78 (0.26 cuft)

6014MR

6314MR

3/4"



6314MR

14
PC.

KT NO.

Contents



13.8



1

6014MR	6330M	22, 24, 27, 30, 32, 36, 38, 41, 46, 50	6779-20F	6251-08 6251-16	6572-20
6314MR	6335M				

6016MR

Metal case size (mm) :
537 x 177 x 78 (0.26 cuft)

6316MR

6316MR

6016SR

3/4"



6016MR/6016SR

16
PC.

KT NO.

Contents



14.0



1

6016MR	6330M	21, 22, 23, 24, 27, 30, 32, 36, 38, 41, 46, 50	6779-20F	6251-08 6251-16
6316MR	6335M			
6016SR	6330S	7/8, 15/16, 1, 1-1/16, 1-1/8, 1-1/4, 1-3/8, 1-1/2, 1-5/8, 1-3/4, 1-7/8, 2	6572-20	