

Long Nose Pliers

6315

- ASME B107.500-2010

MATERIAL - Jaw : Spring alloy steel

Handle : Chrome molybdenum alloy steel

KT NO.	Overall length inch	mm	Jaw capacity mm		
6315-06	6	166	51	186	8 / 80
6315-09	9	221	70	393	6 / 36



Locking Pliers Set

KT NO.	PC.	Contents		
42503PR	3	 6011-10R  6031-07R	1.24	1 / 20
42504PR	4	 6011-05R  6013-10R  6315-06	1.43	1 / 15



► Nylon pouch bag

Lock Sheet Metal Clamp

6605

- With adjusting screw and release lever
- Makes bending, forming, and crimping sheet metal easier

MATERIAL - Chrome molybdenum alloy steel



KT NO.	Overall length inch	mm	Jaw capacity mm		
6605-08	8	206	13	475	1 / 18

Locking Welding Clamp

6665

- U-shaped jaws allow enhanced visibility and more working space
- Holds work in proper alignment
- For use in welding or holding awkward shapes in place

MATERIAL - Chrome molybdenum alloy steel



KT NO.	Overall length inch	mm	Capacity mm		
6665-09	9	230	70	622	1 / 18

Locking Chain Clamp

6655

- Chain can hold around any shape or size
- Convenient for awkward shaped pieces
- With adjusting screw and release lever

MATERIAL - Handle : Chrome molybdenum alloy steel

KT NO.	Overall length inch	mm	Capacity mm		
6655-09	9	225	Ø 60~140	733	1 / 18

