

Power Driving

- Silicon chrome vanadium alloy steel (S2)
- Nickel plated
- Magnetic

1/4" Hex size shank driver



order unit : one box

1300P



- Long head type



KT NO.	⊕ No.	Overall length (mm)	g	13	10 / 300
134501P	PH1	45	8		10 / 300
134502P	PH2	45	9		10 / 300
134503P	PH3	45	9		10 / 300
136501P	PH1	65	14		10 / 200
136502P	PH2	65	14		10 / 200
136503P	PH3	65	14		10 / 200
131101P	PH1	110	26		10 / 150
131102P	PH2	110	26		10 / 150
131103P	PH3	110	26		10 / 150
131501P	PH1	150	36		10 / 100
131502P	PH2	150	36		10 / 100
131503P	PH3	150	37		10 / 100

1500P



- Short head type



KT NO.	⊕ No.	Overall length (mm)	g	9	10 / 300
155001P	PH1	50	10		10 / 300
155002P	PH2	50	10		10 / 300
155003P	PH3	50	10		10 / 300
157501P	PH1	75	16		10 / 200
157502P	PH2	75	16		10 / 200
157503P	PH3	75	17		10 / 200
151001P	PH1	100	23		10 / 150
151002P	PH2	100	23		10 / 150
151003P	PH3	100	23		10 / 150
151501P	PH1	150	36		10 / 100
151502P	PH2	150	37		10 / 100
151503P	PH3	150	37		10 / 100

7300P



- Long head type



KT NO.	⊕ No.	Tip width (mm)	Tip thickness (mm)	Overall length (mm)	g	13	10 / 300
734551P	PH1	5.0	0.8	45	8		10 / 300
734552P	PH2	5.0	0.8	45	8		10 / 300
736552P	PH2	5.0	0.8	65	13		10 / 200
731152P	PH2	5.0	0.8	110	25		10 / 150
731552P	PH2	5.0	0.8	150	36		10 / 100

- Silicon chrome vanadium alloy steel (S2)
- Anti-rust oiled, phosphate sunk
- Magnetic

1/4" Hex size shank driver



order unit : one box

13A6502P



- Long head type
- For ironwork screws



KT NO.	⊕ No.	Overall length (mm)	g	13	10 / 100
13A6502P	PH2	65	8		10 / 100

13B6502P



- Long head type
- For woodwork screws



KT NO.	⊕ No.	Overall length (mm)	g	13	10 / 100
13B6502P	PH2	65	8		10 / 100

- Chrome vanadium & stainless alloy steel
- Anti-rust oiled, sand-blasted
- Magnetic

1/4" Hex size shank driver



750

750-50A



- Magnetic bit holder
- 750-50A : with spring clip
- DIN 7427



KT NO.	⊕ No.	Overall length (mm)	g	13	10 / 300
750-60	1/4	60	20		6 / 84
750-50A	1/4	50	22		6 / 84

KT NO.	⊕ No.	Overall length (mm)	g	13	10 / 300
750-75	1/4	75	30		1 / 20
750-100	1/4	100	37		1 / 20
750-150	1/4	150	50		1 / 20

751



- Magnetic bit holder
- With spring clip
- DIN 7427



KT NO.	⊕ No.	Overall length (mm)	g	13	10 / 300
751-60	1/4	60	24		6 / 84
751-75	1/4	75	36		6 / 84

