

Ratchet Tubing Cutter for PVC Pipe

7913

- For PVC, PP, PE, PEX, PB pipes
- Ratchet design for quick cutting



KT NO.	inch	mm	Overall length			
			inch	mm	g	box / cube
7913-42	1/2~1-5/8	6~42	8	201	360	10 / 50
7913-4211	Spare cutting blade				60	10 / 200



2-in-1 Ratchet Tubing Cutter for PVC Pipe

7913A-63

- Easy one-hand operation
- Cut into thick pipe and thin pipe
- Easily apply for max. 63 O.D.
- Comfortable TPR handle
- For unitary material tube: PE, PP, PVDF, PB, PVC or similar tube
- Advanced tool steel blade and aluminum body
- Ratchet design for quick cutting




KT NO.	inch	mm	Overall length			
			inch	mm	g	box / cube
7913A-63	1/4~2-1/2	6~63	11-1/2	293	802	6 / 24
7913A-6311	Spare cutting blade				190	1 / 100

S Type Pipe Wrench

6521

- For nuts, bolts, flat material
- A non-detachable adjusting nut with round thread ensures a wide adjustment
- For working in confined space
- DIN 5234




KT NO.	A	Size	Overall length			
	mm	inch	inch	mm	g	box / cube
6521-13	40	1	13	330	791	1 / 20
6521-16	55	1-1/2	16-1/2	420	1450	1 / 12
6521-21	67	2	21	535	2404	1 / 6
6521-26	103	3	25-5/8	652	5030	1 / 2

Pipe Wrench

6531

- Professional stillson type
- High quality steel



KT NO.	inch	mm	Overall length			
			inch	mm	g	box / cube
6531-10	1-3/16	34	10	231	600	1 / 24
6531-12	1-9/16	42	12	271	780	1 / 24
6531-14	1-7/8	48	14	315	1050	1 / 12
6531-18	2-3/8	60	18	407	1720	1 / 12
6531-24	2-15/16	76	24	539	3150	1 / 6
6531-36	4	102	36	825	6280	1 / 2
6531-48	5-1/2	140	48	1034	9750	1 / 2