


Socket Set

8330M

1"

- DIN 3124, ISO 2725-1




KT NO.	Ø mm	D1 mm	D2 mm	ℓ mm	L mm	⚖	📦
833036M	36	52	48	26	65	514	1 / 24
833038M	38	54	48	26	65	536	1 / 24
833041M	41	58	50	29	70	659	1 / 24
833046M	46	65	54	32	75	961	1 / 24
833050M	50	70	54	34	75	985	1 / 20
833054M	54	74	57	38	80	1164	1 / 20
833055M	55	76	57	42	83	1256	1 / 12
833058M	58	79	57	42	83	1263	1 / 12
833060M	60	82	58	46	87	1488	1 / 12
833063M	63	86	58	46	87	1548	1 / 12
833065M	65	88	65	49	90	1817	1 / 12
833067M	67	91	70	49	91	1932	1 / 12
833070M	70	94	70	50	93	2064	1 / 8
833071M	71	95	70	50	93	2026	1 / 8
833075M	75	100	70	50	95	2168	1 / 8
833077M	77	103	80	52	100	2732	1 / 8
833080M	80	107	80	52	100	3009	1 / 8

8330S

1"

- ANSI / ASME B107.1



KT NO.	Ø inch	D1 mm	D2 mm	ℓ mm	L mm	⚖	📦
833046S	1-7/16	52	48	26	65	506	1 / 24
833048S	1-1/2	54	48	26	65	537	1 / 24
833054S	1-11/16	60	54	29	70	741	1 / 24
833060S	1-7/8	67	54	34	75	912	1 / 10
833064S	2	71	54	34	75	989	1 / 10
833072S	2-1/4	78	57	42	83	1267	1 / 12
833076S	2-3/8	82	58	46	87	1452	1 / 12
833084S	2-5/8	90	65	49	90	1825	1 / 12
833094S	2-15/16	100	70	52	95	2076	1 / 8
8330A0S	3-1/8	107	80	52	100	2975	1 / 8

Ratchet

8779

1"

- Reversible ratchet
- 15° gear action degree (24 teeth)
- DIN 3122



8779DK



KT NO.	Overall length inch	mm	⚖	📦
8779-32F	32	800	4400	5
8779DK	renewal kits	-	-	-

Accessory

- Chrome vanadium handle, chrome molybdenum driver
- Chrome plated handle & black phosphate sunk driver

8251

1"

- Extension bar
- DIN3123



KT NO.	Overall length inch	mm	⚖	📦
8251-08	8	200	1364	1 / 16
8251-16	16	400	2555	1 / 10

8572

1"

- Sliding T-handle
- DIN 3122



8572DK



KT NO.	Overall length inch	mm	⚖	📦
8572-25	25	630	4200	6
8572DK	renewal kits	-	-	-

8581

1"

- L-handle
- DIN 3122



KT NO.	Overall length inch	mm	⚖	📦
8581-26	26	660	5182	4

8816

1"

- Adapter
- Convert to 3/4" drive
- Max. torque : 1412 N-m
- DIN 3123, ISO 3316



KT NO.	Spec.	⚖	📦
8816	1" F x 3/4" M	309	6 / 48